

BBBF36 STANDARD INSTALLATION DIMENSIONS


Notes:

Except where noted, dimensions shown are from enclosure to refrigerator Dimensions shown in [] are in millimeters

(A) If depth is greater than 24", add shims as needed for anchor bracket.

BBBF36 STANDARD INSTALLATION DIMENSIONS






Notes:

Except where noted, dimensions shown are from enclosure to refrigerator Dimensions shown in [] are in millimeters

(A) Recommended minimum side wall clearance of 5" for 90° door opening (B) Recommended minimum side wall clearance of 11-11/16" for 115° door opening

BBBF36 STANDARD INSTALLATION DIMENSIONS






Notes: Dimensions shown in [] are in millimeters

(A) Recommended enclosure height based on installation method: 83-I/4'' - 84''

(B) Dimensions shown are with rollers in minimum position as shipped. Unit can be raised I" max.




DETAIL E

- Dimensions shown in [] are in millimeters
- (A) If depth is greater than 25-9/16", add shims as needed for anchor bracket.
- If door protrudes less than 3/4", door will not open properly, and damage to enclosure may occur.
- BI If decorative trim or other element is applied to front of enclosure, it must be at least I-3/4" away from enclosure opening.

BBBF36 LOW PROFILE INSTALLATION DIMENSIONS





Notes:

Except where noted, dimensions shown are from enclosure to refrigerator Dimensions shown in [] are in millimeters


(A) Dimension shown based on an enclosure depth of 25-9/16". If the enclosure is shallower, adjust dimension accordingly.

(B) Recommended minimum side wall clearance of 4-3/4" for 90° door opening

(C) Recommended minimum side wall clearance of 11-7/16" for 115° door opening

BBBF36 LOW PROFILE INSTALLATION DIMENSIONS





Notes: Dimensions shown in [] are in millimeters


(A) Recommended enclosure height based on installation method: *83-1/2" - 84"*


(B) Dimensions shown are with rollers in minimum position as shipped. Unit can be raised I" max.

BBBF36 FLUSH INSTALLATION DIMENSIONS



Enclosure Dimensions






Notes:

Except where noted, dimensions shown are from enclosure to refrigerator Dimensions shown in [] are in millimeters

(A) If depth is greater than 26-5/16", add shims as needed for anchor bracket

BBBF36 FLUSH INSTALLATION DIMENSIONS






Notes:

Except where noted, dimensions shown are from enclosure to refrigerator Dimensions shown in [] are in millimeters

(A) Recommended minimum side wall clearance of 3" for 90° door opening (B) Recommended minimum side wall clearance of 9-11/16" for 115° door opening

BBBF36 FLUSH INSTALLATION DIMENSIONS





Notes: Dimensions shown in [] are in millimeters

(A) Recommended enclosure height based on installation method: 83-1/2" - 84"

(B) Dimensions shown are with rollers in minimum position as shipped. Unit can be raised I" max.